

The plate placement unit TELAL-01 for continuous operation with an automatic changing function. Product information: Technical data:

Continuous operation: The plate placement module consists of two trolley garages. This allows the option of having a single plate type placed continuously.

The empty dispenser trolley is changed during operation. The unit switches from the empty to the full dispenser trolley automatically. **Individual:** Alternatively, two different plate types can be placed.

Hygienic: The plates are continuously and individually removed from the plate dispenser trolley by a suction gripper arm and placed at a defined position on the tray.

Technical data:	
Connected load:	ca. 2 KW
Required compressed air:	ca. 80 I/min.
Dimensions (depending on the dispenser trolley) (L x W x H):	approx. 3,400 x 980 x 1,800 mm
Output:	approx. 15 plates per minute
By request, the TELAL-01 is also available with four or six tray garages.	